

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P18B24M	4.6kg

**SPECIFICATION:**






1. STANDARD:
- |                      |                        |
|----------------------|------------------------|
| UNIT TYPE:           | BASIC                  |
| ORIENTATION:         | VERTICAL, HALF         |
| OUTLET QTY&TYPE:     | (18) C13               |
| INPUT VOLTAGE:       | 100-120/200-240VAC     |
| INPUT CURRENT:       | 30A (24A DERATED)      |
| BREAKER QTY&TYPE:    | (3) 20AMP, DOUBLE-POLE |
| INPUT PHASE:         | THREE-PHASE WYE        |
| RATED POWER:         | 8.6kVA                 |
| INPUT PLUG:          | NEMA L21-30P           |
| INPUT POWER CORD:    | 3m [10'], TOP FEED     |
| REGULATORY STANDARD: | RoHS COMPLIANT         |
2. ADDITIONAL: NONE
3. ACCESSORIES: POCKET GUIDE

**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN INCHES
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- OUTLETS ARE WIRED LINE TO LINE (208V)

**IDENTIFICATION**

PART NUMBER	DESCRIPTION
P18B24M	BASIC PDU, 30AMP, (18)C13, NEMA L21-30P-3M, BLACK



**PLUG/RECEPTACLE BLOCK**

**PLUG**  
NEMA L21 - 30P, 4P 5W  
30A, 120/208V MAX RATED INPUT  
24A DERATED

**RECEPTACLES**  
IEC 60320/C13  
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02C	04/08/2022	CWW	MIM	JAWI	ADDED*OUTLETS ARE WIRED LINE TO LINE (208V)*IN NOTE 5	P18B24M
02B	05/26/2020	Leo	MIM	JAWI	UPDATED THE DESCRIPTION & UPDATED THE OUTLET DESIGN	P18B24M
01B	08/21/2017	JIANG	MIM	EDM	REVISED TOLERANCES	P18B24M
01A	06/28/2017	JIANG	MIM	EDM	INITIAL RELEASE	P18B24M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE BASIC SERIES PDU P18B24M CUSTOMER DRAWING		
ITEM REVISION NAME		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER: P18B24M_DC
DRAWN BY	DATE	SCALE
JIANG	05/24/2017	NONE
CHK	SCALE	SHT 1 OF 1
SEAN	NONE	B