







NOTES, UNLESS OTHERWISE SPECIFIED:

PANDUIT PART NO.: UPS003LSM
(LOAD SENSE MODULE)

Input Power
Voltage: 30.0 VDC Max.
Current: 5 A max.


Output Power
Voltage: 30.0 VDC Max.
Sense: 100 mV max.
Current: 5 A max.

Environmental
Operating Temperature: -40°C to +60°C.
Storage (non-operational) Temperature: -40°C to +70°C.
Humidity: 0 to 95% RH, noncondensing
Operational Vibration: 2G at 10 to 500 Hz
Operational Shock: 20G (11ms 3 bumps / direction,
18 bumps in total)

Weight: 105.72 gr. / 0.233 lbs.

Numbers in parentheses () are inches.

F:\wrkgrp\rvusers\ENGR DOCS\LABEL DRAWINGS\FG27233C01_01
UPS003LSM CUST DWG..doc

							UPS003LSM (LOAD SENSE MODULE)					
							CUSTOMER DRAWING					
							ITEM REVISION NAME: FG27233C01_01				PANDUIT	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:				MATERIAL: SEE NOTES	
01	2-11-14	BLR	SILD	ALP	UPDATE I/O VOLTAGES	4628	(.x) ± ---	(.xxx) ± ---				
00	10-11-13	BLR	SILD	ALP	RELEASED	4606	(.xx) ± ---	ANGLES ± ---				
									THIRD ANGLE PROJECTION		DRAWING NUMBER: FG27233C01	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY: BLR	DATE: 10-11-13	CHK SILD	SCALE NONE	SHT 1 OF 1	SIZE C