

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER	WIRE SIZE AWG [mm ²]	STUD SIZE		HOUSING COLOR	DIMENSIONS - in. [mm]						WIRE STRIP LENGTH in [mm] +1/32 [0,8] -0	TOOLS
		ENGLISH	METRIC		L± .04 [1,1]	B	W± .01 [0,3]	C± .01 [0,3]	M± .02 [0,6]	H+.01 [0,3] -0		
EV14-6FNB	#16-14 [1.5-2.5]	#6	M3.5	BLUE	.83 [21.0]	.165 [4.2]	.22 [5.7]	.26 [6.5]	.39 [10.0]	0.146 [3.7]	9/32" [6.8]	KST2000A
EV14-8FNB	#16-14 [1.5-2.5]	#8	M4		.83 [21.0]	.165 [4.2]	.28 [7.2]	.26 [6.5]	.39 [10.0]	0.169 [4.3]		
EV14-10FNB	#16-14 [1.5-2.5]	#10	M5		.83 [21.0]	.165 [4.2]	.31 [7.9]	.26 [6.5]	.39 [10.0]	0.209 [5.3]		
EV10-8FNB	#12-10 [4.0-6.0]	#8	M4	YELLOW	1.00 [25.5]	.240 [6.1]	.33 [8.3]	.28 [7.0]	.51 [13.0]	0.169 [4.3]	11/32" [8.8]	
EV10-10FNB	#12-10 [4.0-6.0]	#10	M5		1.00 [25.5]	.240 [6.1]	.35 [9.0]	.28 [7.0]	.51 [13.0]	0.209 [5.3]		

NOTES :


1. UL LISTED FOR:
A. STRANDED COPPER WIRE ONLY
B. 221°F (105°C) MAX TEMP RATING
C. 600V MAX VOLTAGE RATING
2. MATERIAL:
A. STAMPING - COPPER, TIN PLATED:
 EV14 - .031" [0,8] THICK
 EV10 - .039" [1,0] THICK
B. HOUSING - VINYL
3. SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
4. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



LISTED
20U0
E52164



00	2/18	JHNU	TMR	RGB	DRAWING RELEASED	00123SS
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					STRONGHOLD NARROW FORK TERMINALS, VINYL INSULATED, BUTTED SEAM #16-10 AWG	
ITEM REVISION NAME					CUSTOMER DRAWING	
00123SSL/00						
DATASET FILE NAME						
00123SSL_DC/00					MATERIAL: SEE NOTES	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± ANGLES ±					DRAWING NUMBER: 00123SSL - DC	
 THIRD ANGLE PROJECTION					DRAWN BY: FES DATE: - CHK: FES SCALE: N.T.S.	
SHEET 1 OF 1					SIZE: A	