


Bronze Vi-Tite Terminal Lugs - Two or Four Hole Tongue Type VL3


For use with three copper conductors

- Manufactured from high strength copper alloy for maximum conductivity and corrosion resistance
- Heavy duty terminals used for joining a wide range of copper conductors to equipment pads or bus bars
- Bronze screw and pressure bar provide uniform clamping pressure on conductor
- Two and four hole mounting pads allow for maximum surface contact in heavy duty applications
- Annular serrations in conductor grooves provide improved mechanical performance
- Inspection hole allows for visual confirmation of proper cable insertion
- Hex head screws can be furnished on request by adding suffix “-HH” to catalog number
- For tin plating, suffix catalog number with “-TN”



2 Hole Tongue

CATALOG NUMBER	CONDUCTOR RANGE	APPROXIMATE DIMENSIONS (IN.)						MTG. BOLT SIZE	HEX SIZE
		L	M	W	H	G	T		
VL3-21766	4 Sol. - 1 Str.	3.94	1.88	1.50	.88	3.13	.25	1/2	3/16
VL3-21768	2 Str. - 2/0 Str.	4.00	2.19	1.63	1.03	3.13	.22		1/4
VL3-21774	1/0 Str. - 4/0 Str.	4.25	2.63	1.88	1.28	3.13	.25		1/4
VL3-21782	3/0 Str. - 350 kcmil	4.31	2.88	1.50	1.38	3.13	.31		3/8
VL3-21785	300 - 500 kcmil	4.50	3.50	2.50	1.81	3.13	.38		3/8
VL3-21790	500 - 800 kcmil	4.63	4.19	2.50	1.81	3.13	.44		3/8
VL3-21795	700 - 1000 kcmil	5.31	4.63	2.50	2.06	3.25	.50		3/8
VL3-21797	1000 - 1500 kcmil	6.00	6.00	2.50	2.31	3.13	.63		1/2
VL3-21799	1500 - 2000 kcmil	6.13	6.75	3.00	2.69	3.13	.63		1/2



4 Hole Tongue

CATALOG NUMBER	CONDUCTOR RANGE	APPROXIMATE DIMENSIONS (IN.)						MTG. BOLT SIZE	HEX SIZE
		L	M	W	H	G	T		
VL3-21918	3/0 Str. - 350 kcmil	4.31	2.88	3.00	1.38	3.13	.31	1/2	3/8
VL3-21919	300 - 500 kcmil	4.44	3.50	3.00	1.81	3.13	.38		3/8
VL3-21921	500 - 800 kcmil	4.63	4.19	3.00	1.81	3.13	.50		3/8
VL3-21925	700 - 1000 kcmil	5.31	4.63	3.00	2.06	3.25	.50		3/8
VL3-21926	1000 - 1500 kcmil	6.00	6.00	3.50	2.31	3.13	.63		1/2
VL3-21928	1500 - 2000 kcmil	6.13	6.75	4.00	2.69	3.13	.63		1/2

