

**NEW
PRODUCT**

Bronze Ground Clamps with Adapter Types KG & KG-DB

- Cast from high strength, high conductivity copper alloy
- Designed to connect bare copper or armored copper wire to galvanized steel or copper water pipe
- 360° integral clamp securely holds armor in place and allows for easy alignment
- Type KG-DB are suitable for direct burial applications
- Standards: UL 467, CSA C22.2NO.41



CATALOG NUMBER	WATER PIPE RANGE	CONDUCTOR RANGE	SCREW MATERIAL
KG-1 •	1/2" - 1"	8 Str. - 4/0 Str.	Zinc Plated Steel
KG-2 •	1-1/4" - 2"		
KG-3 •	2-1/2" - 4"		
KG-4 •	4-1/2" - 6"		
KG-1-DB *	1/2" - 1"		Bronze
KG-2-DB *	1-1/4" - 2"		
KG-3-DB *	2-1/2" - 4"		
KG-4-DB *	4-1/2" - 6"		

• Listed * Listed

Bronze Ground Clamps for Armored Cable with 360° Swivel Hub

Type KW

- Cast from high strength, high conductivity copper alloy
- Designed to connect bare copper or armored copper wire to galvanized steel or copper water pipe
- 360° integral clamp securely holds armor in place and allows for easy alignment
- Standards: UL 467, CSA C22.2NO.41



CATALOG NUMBER	WATER PIPE RANGE	CONDUCTOR RANGE	SCREW MATERIAL
KW-1	1/2" - 1"	10 Sol. - 6 Str.	Zinc Plated Steel
KW-2	1 1/4" - 2"		
KW-4	2 1/2" - 4"		