



### Model Number


#### V19-G-BK15M-PUR-U/ABG

Female cordset, M12, 8-pin, shielded, PUR cable

### Features

- UL Recognized Component
- Knurled nut suitable for tool assembly
- Immunity to vibration, with mechanical latching
- Flame resistant cable
- Halogen-free
- Shield attached to coupling nut

### Dimensions



### Technical data

#### General specifications

Number of pins	8
UL File Number	E231213

#### Electrical specifications

Operating voltage	$U_B$	max. 30 V DC
Operating current	$I_B$	max. 2 A
Volume resistance		< 5 m $\Omega$

#### Ambient conditions

Ambient temperature	-40 ... 90 °C (-40 ... 194 °F) cable, fixed: -40 ... 80 °C (-40 ... 176 °F) cable, flexing: -20 ... 80 °C (-4 ... 176 °F)
---------------------	---

Pollution degree	3
------------------	---

#### Mechanical specifications

Contact elements	spring-loaded contact socket
Pin diameter	0,8 mm
Degree of protection	IP67

#### Material

Contacts	CuSn / Au
Contact surface	Au
Body	TPU, black
Cable	PUR
Slotted nut	Diecast zinc
Core insulation	PP
Cable	fine-strand, flexible
Sheath diameter	$\varnothing$ 6 mm
Bending radius	> 10 x cable diameter, moving
Color	black
Number of cores	8
Core cross-section	0.25 mm <sup>2</sup>
Conductor construction	14 x 0.15 mm $\varnothing$
Shield	grid covering 85 %
Length	L 15 m

#### Flammability

Contact carrier	94 HB
Housing	94 V-2

#### Approvals and certificates

UL approval	cURus AWM 20549 AWM I/II A/B 80°C 300V FT2 (cable)
-------------	--

### Electrical connection

