









|                                   |          |          |                          |         |            |                                |                                                    |                |              |         |        |
|-----------------------------------|----------|----------|--------------------------|---------|------------|--------------------------------|----------------------------------------------------|----------------|--------------|---------|--------|
| Observe protection note to DIN 34 | A        | 20110138 | 05.05.2011               | EP-MK   | EP-MK      | Neue Zeichnung<br>New drawing. |                                                    |                |              |         |        |
|                                   | Index    | ECO no.  | Date                     | Editor  | Checked    |                                |                                                    |                |              |         |        |
|                                   | Scale    | 1:1      |                          |         |            | Date                           | Name                                               | MODEL: 2008425 | DRW: 2008426 |         |        |
|                                   | Material |          |                          | Created | 01.02.2011 | EP-MK                          | Internet Dokument<br>Internet document<br>S99/22.5 |                |              |         |        |
|                                   |          |          |                          | Checked | 01.02.2011 | EP-MK                          |                                                    |                |              |         |        |
|                                   |          |          |                          | Norm    | -          | -                              |                                                    |                |              |         |        |
|                                   |          |          | All dimensions are in mm |         |            |                                |                                                    |                |              |         |        |
|                                   | Surface  |          | Unspecified tolerance    |         |            |                                |                                                    |                | Doc.-No.     | 2008426 | Page 1 |
|                                   |          |          |                          |         |            |                                |                                                    |                | Mat.-No.     | -       | of 1   |

