

PSSu K S 16DO 0.5

312432



Compact module, with standard function, 16 digital outputs (0.5 A).

Technical details


Certifications:	CE;cULus Listed;BG;TÜV
Application range:	Standard
Positive switching 1-pole SC output:	16
Protection type, housing:	IP20
Width dimension:	30.0 mm
Height dimension:	128.9 mm
Depth dimension:	56.0 mm
Gross weight:	105 g
Net weight:	92 g
Ambient temperature:	0 - 60 °C

Accessories



313115

PSSu A Con 1/10 C (2 pcs.)



313116

PSSu A Con 3/30 C (2 pcs.)

Optional accessories



312900

PSSu A ET (10 pcs.)



312901

PSSu A ETM (2 pcs.)



312902

PSSu A EC



312949

PSSu A ET PE (10 pcs.)



312958

PSSu A LA0 (10 x 108 pcs.)



312967

PSSu A LA0.1 (10 x 108 pcs.)



312966

PSSu A LC 0.1 (5 pcs.)