

PSSu E F PS-P-R

315185



Electronic module for voltage distribution (periphery 24 V), railway.

Technical details

Certifications:	CE;TÜV
Application range:	Standard/failsafe
Permitted base modules:	PSSu BS 1/8C;PSSu BS 1/8S
Width dimension:	12.6 mm
Height dimension:	76.0 mm
Depth dimension:	60.2 mm
Gross weight:	40 g
Net weight:	35 g
Ambient temperature:	-40 - 70 °C

Accessories



314650

PSSu BS 1/8 S-T



314651

PSSu BS 1/8 C-T

Optional accessories



312900

PSSu A ET (10 pcs.)



312901

PSSu A ETM (2 pcs.)



312949

PSSu A ET PE (10 pcs.)



312958

PSSu A LA0 (10 x 108 pcs.)



312967

PSSu A LA0.1 (10 x 108 pcs.)



314902

PSSu A EC-T