

PSSu E F 4DI-R

315200



Electronic module digital inputs and outputs, with failsafe function, 4 inputs, 24 V, railway.

Technical details

Certifications:	CE;TÜV
Application range:	Failsafe
Number of digital inputs:	4
Number of test pulse outputs:	2
Protection type, housing:	IP20
Permitted base modules:	PSSu BP 1/12C-T;PSSu BP 1/12S-T;PSSu BP 1/8C-T;PSSu BP 1/8S-T;PSSu BP-C1 1/12C-T;PSSu BP-C1 1/12S-T
Width dimension:	12.6 mm
Height dimension:	76.0 mm
Depth dimension:	60.2 mm
Gross weight:	44 g
Net weight:	36 g
Ambient temperature:	-40 - 70 °C

Accessories



314600

PSSu BP 1/8 S-T



314601

PSSu BP 1/8 C-T



314618

PSSu BP 1/12 S-T

314619

PSSu BP 1/12 C-T



314622

PSSu BP-C1 1/12 S-T



314623

PSSu BP-C1 1/12 C-T

Optional accessories



312900

PSSu A ET (10 pcs.)



312901

PSSu A ETM (2 pcs.)



312949

PSSu A ET PE (10 pcs.)



312958

PSSu A LA0 (10 x 108 pcs.)



312967

PSSu A LA0.1 (10 x 108 pcs.)



314902

PSSu A EC-T