

PSSu E F 2DOR 8-R

315225



Electronic module digital inputs and outputs, with failsafe function, 2 relay outputs, potential-free 8 A, railway.

Technical details

Certifications:	CE;TÜV
Application range:	Failsafe
Number of relay outputs:	2
Protection type, housing:	IP20
Permitted base modules:	PSSu BP 2/16C-T;PSSu BP 2/16S-T;PSSu BP-C 2/16C-T;PSSu BP-C 2/16S-T
Width dimension:	25.2 mm
Height dimension:	76.0 mm
Depth dimension:	60.2 mm
Gross weight:	100 g
Net weight:	93 g
Ambient temperature:	-40 - 70 °C

Accessories



314628

PSSu BP 2/16 S-T



314629

PSSu BP 2/16 C-T



314630

PSSu BP-C 2/8 S-T



314631

PSSu BP-C 2/8 C-T

Optional accessories



312900

PSSu A ET (10 pcs.)



312901

PSSu A ETM (2 pcs.)



312949

PSSu A ET PE (10 pcs.)



312958

PSSu A LA0 (10 x 108 pcs.)



312967

PSSu A LA0.1 (10 x 108 pcs.)



314902

PSSu A EC-T