

PSS67 Cable M12af M12am, 30m

380215



PSS67 cable, M12 female connector angled to M12 male connector straight, 30 m.

Technical details

Rated current:	4.0 A
Number of conductors:	5
Shielding:	No
Conductor cross section:	0,25
Drag capacity:	No
Length cable:	30.00 m
Certifications:	cULus Listed
Ambient temperature:	-25 - 80 °C
Degree of protection connector 1:	IP68
Degree of protection connector 2:	IP68