

PSS67 Supply Cable IN sf, B, 3m

380256



PSS67 distribution cable (IN) straight female connector, B coded, 3 m.

Technical details

Rated current:	4.0 A
Number of conductors:	5
Shielding:	No
Conductor cross section:	0,50
Drag capacity:	Yes
Length cable:	3.00 m
Certifications:	cULus Listed
Ambient temperature:	-25 - 80 °C
Degree of protection connector 1:	IP68