

PIT esc2c

400321



PITestop contact block 1 N/C with spring-loaded terminal.

Technical details

Certifications:	CE;EAC (Eurasian);TÜV;CSA
Product standard:	EN 60947-5-5;EN ISO 13850
Terminal type:	Spring-loaded terminal
Self-monitored:	No
Number of N/C:	1
Max. current at AC15:	3.0 A
Voltage at AC15:	250 V
Max. current at DC13 I (6 cycles/min):	2.0 A
Voltage at DC13:	24 V
Width dimension:	44.0 mm
Height dimension:	30.0 mm
Depth dimension:	10.0 mm
Gross weight:	11 g
Net weight:	9 g
Ambient temperature:	-25 - 55 °C