

PIT es3u

400533



PITestop E-STOP pushbutton IP65, illuminated, without logo, mounting hole: 22.3 mm.

## Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Product standard:	EN 60947-5-5;EN ISO 13850
Release type:	Rotational
Actuator:	Pushbutton
Colour button:	Red
Protective collar:	No
Terminal type:	Screw terminal
Supply voltage (V):	12,0 - 30,0
Supply voltage type:	AC/DC
Protection type, housing:	IP65
Mounting type:	Front panel installation
Diameter of mounting cut-out:	22.3 mm
Width dimension:	56.0 mm
Height dimension:	60.0 mm
Gross weight:	66 g
Net weight:	53 g
Ambient temperature:	-25 - 55 °C