

PIT en1.0p-5m-s

401110



PITenable 3-step enabling switch, 5 m connection cable and M12 angled connector.

Technical details

Certifications:	CE
Attachment:	Magnetic clamp
Mounting position:	Any
Number of N/O:	2
Max. current at DC13 I (6 cycles/min):	0.7 A
Voltage at DC13:	30 V
Max. current at DC12:	1.0 A
Voltage at DC12:	30 V
Connection type:	M12, 5pol. male, gewinkelt
Protection type, housing:	IP65
Diameter:	45.0 mm
Width dimension:	45.0 mm
Height dimension:	125.0 mm
Depth dimension:	45.0 mm
Gross weight:	409 g
Net weight:	383 g
Ambient temperature:	0 - 50 °C