

PSEN 1.1p-29/PSEN 1.1-20/7mm/ix1/ 1unit

504224



Magnetic safety switch 2 N/O, 4-pin M8 male connector, square design. Height design 13 mm IP67, operating distance 7 mm, for applications with PSEN ix1 PU = 1 piece with actuator Special version without 0.5 mm latched zone.

## Technical details

Housing material:	PBT
Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Sensor principle:	magnetic
Number of N/O:	2
Connection type:	M8, 4pol. male
Switching voltage:	24 V
Type of switching voltage:	DC
Assured switching distance:	7.0 mm
Assured release distance:	26.0 mm
Protection type, housing:	IP65;IP67
Status indicator:	Without LED
Design:	square
Width dimension:	26.0 mm
Height dimension:	42.8 mm
Depth dimension:	13.0 mm
Gross weight:	44 g
Net weight:	36 g
Ambient temperature:	-10 - 55 °C
Operating modes:	Series connection

## Accessories



533110

PSEN Kabel Winkel/cable angleplug 2m



533111

PSEN Kabel Gerade/cable straightplug 2m



533120

PSEN Kabel Winkel/cable angleplug 5m



533121

PSEN Kabel Gerade/cable straightplug 5m



533130

PSEN Kabel Winkel/cable angleplug 10m



533131

PSEN Kabel Gerade/cable straightplug 10m



533140

PSEN Kabel Winkel/cable angleplug 30m



533141

PSEN Kabel Gerade/cable straightplug 30m



535120

PSEN ix1 Interface for 4 PSEN 1

## Optional accessories



532110

PSEN Winkel / bracket



533110

PSEN Kabel Winkel/cable angleplug 2m



533111

PSEN Kabel Gerade/cable straightplug 2m



533120

PSEN Kabel Winkel/cable angleplug 5m



533121

PSEN Kabel Gerade/cable straightplug 5m



533130

PSEN Kabel Winkel/cable angleplug 10m



533131

PSEN Kabel Gerade/cable straightplug 10m



533140

PSEN Kabel Winkel/cable angleplug 30m



533141

PSEN Kabel Gerade/cable straightplug 30m



534310

PSEN Distanzplatte / spacer (10 pcs.)

---



534320

PSEN reverse spacer

---



535120

PSEN ix1 Interface for 4 PSEN 1

---



540310

PSEN screw M4x16 10pcs

---