

PSEN ma1.4-51M12/8-0.15m/PSENma1.4-03/1u

506344



Magnetic safety switch 2 N/O, 1 signal contact N/O, 8-pin M12 connector, square design, LED IP67, operating distance 3 mm, height design 18 mm  
PU = 1 sensor with actuator.

## Technical details

Housing material:	PBT
Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Sensor principle:	magnetic
Number of N/O:	2
Connection type:	M12, 8pol. male
Switching voltage:	24 V
Type of switching voltage:	DC
Assured switching distance:	3.0 mm
Assured release distance:	12.0 mm
Protection type, housing:	IP65;IP67
Status indicator:	With LED
Design:	square
Width dimension:	26.4 mm
Height dimension:	37.0 mm
Depth dimension:	18.0 mm
Gross weight:	90 g
Net weight:	51 g
Ambient temperature:	-10 - 55 °C
Operating modes:	Single connection

## Accessories



540319

PSEN cable axial M12 8-pole 3m



540320

PSEN cable axial M12 8-pole 5m



540321

PSEN cable axial M12 8-pole 10m



540322

PSEN cable angle M12 8-pole 3m



540323

PSEN cable angle M12 8-pole 5m



540324

PSEN cable angle M12 8-pole 10m



540325

PSEN cable angle M12 8-pole 30m



540326

PSEN cable axial M12 8-pole 30m



540333

PSEN cable M12-8sf, 20m

## Optional accessories



380208

PSS67 Cable M12sf M12sm, 3m



380209

PSS67 Cable M12sf M12sm, 5m



380210

PSS67 Cable M12sf M12sm, 10m



380211

PSS67 Cable M12sf M12sm, 30m



380212

PSS67 Cable M12af M12am, 3m



380213

PSS67 Cable M12af M12am, 5m



380214

PSS67 Cable M12af M12am, 10m












380215

PSS67 Cable M12af M12am, 30m



630297

PSEN op cable axial M12 5-pole 30m

	630310	PSEN op cable axial M12 5-pole 3m
	630311	PSEN op cable axial M12 5-pole 5m
	630312	PSEN op cable axial M12 5-pole 10m
	630347	PSEN op cable angle M12 5-pole 3m
	630348	PSEN op cable angle M12 5-pole 5m
	630349	PSEN op cable angle M12 5-pole 10m
	630350	PSEN op cable angle M12 5-pole 30m
	380220	PSS67 cable M12-5sf, M12-5sm, 20m
	630298	PSEN cable M12-5sf 20m



380713

PDP67 Cable M12-5sf M12-5sm, 2m



380710

PDP67 Cable M12-5sf M12-5sm, 0.5m



380712

PDP67 Cable M12-5sf M12-5sm, 1.5m



380711

PDP67 Cable M12-5sf M12-5sm, 1m



630365

PSEN op cable angle M12 5-pole 50m



630364

PSEN op cable axial M12 5-pole 50m