


PSEN ma1.4p-59/PSEN ma1.4-10 1unit

506348



Safety switch for movable guard's position monitoring in accordance to EN 60947-5-3; 2x no, 1x aux. contact (no), LED; plug M8/8pin with 50mm pigtail; for applications up to SIL3/PL e/Cat4; square design 2009; IP67; Content= 1 switch, 1 actuator; Sao=10mm

## Technical details

Housing material:	PBT
Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Sensor principle:	magnetic
Number of N/O:	2
Connection type:	M8, 8pol. male
Switching voltage:	24 V
Type of switching voltage:	DC
Assured switching distance:	10.0 mm
Assured release distance:	22.0 mm
Protection type, housing:	IP65;IP67
Status indicator:	With LED
Design:	square
Width dimension:	26.4 mm
Height dimension:	37.0 mm
Depth dimension:	18.0 mm
Gross weight:	59 g
Net weight:	43 g
Ambient temperature:	-10 - 55 °C
Operating modes:	Single connection

## Optional accessories



533150

PSEN cable M8-8sf, 2m



533151

PSEN cable M8-8sf, 5m



533152

PSEN cable M8-8sf, 10m



533153

PSEN cable M8-8sf, 20m



533154

PSEN cable M8-8sf, 30m



533155

PSEN cable M8-8sf M8-sm, 0.5m



533156

PSEN cable M8-8sf M8-8sm, 1m



533157

PSEN cable M8-8sf M8-8sm, 2m



535120

PSEN ix1 Interface for 4 PSEN 1



540329

PSEN converter M8-8sf -- M12-8sm



533162

PSEN cable M8-8af, 10m



533159

PSEN cable M8-8sf M8-8sm, 10m



533158

PSEN cable M8-8sf M8-8sm, 5m



533160

PSEN cable M8-8sf M8-8sm, 20m



533161

PSEN cable M8-8sf M8-8sm, 30m