

## PSEN ma1.3p-22/1switch

526127



Magnetic safety switch 3 N/O, M8 connector, round M12 design IP67, for applications with PSEN ix1, PU = 1 piece without actuator.

### Technical details

Housing material:	PBT
Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Sensor principle:	magnetic
Number of N/O:	3
Connection type:	M8, 8pol. male
Switching voltage:	24 V
Type of switching voltage:	DC
Assured switching distance:	8.0 mm
Assured release distance:	15.0 mm
Protection type, housing:	IP65
Status indicator:	With LED
Design:	Round
Depth dimension:	59.1 mm
Gross weight:	38 g
Net weight:	20 g
Ambient temperature:	-25 - 70 °C
Operating modes:	Series connection

## Accessories



533150

PSEN cable M8-8sf, 2m



533151

PSEN cable M8-8sf, 5m



533152

PSEN cable M8-8sf, 10m



533153

PSEN cable M8-8sf, 20m



533154

PSEN cable M8-8sf, 30m



540319

PSEN cable axial M12 8-pole 3m



540320

PSEN cable axial M12 8-pole 5m



540321

PSEN cable axial M12 8-pole 10m



540322

PSEN cable angle M12 8-pole 3m



540323

PSEN cable angle M12 8-pole 5m



540324

PSEN cable angle M12 8-pole 10m



540325

PSEN cable angle M12 8-pole 30m



540326

PSEN cable axial M12 8-pole 30m



540333

PSEN cable M12-8sf, 20m



535120

PSEN ix1 Interface for 4 PSEN 1



516120

PSEN ma1.3-08/1actuator



516130

PSEN ma1.3-12/1actuator

## Optional accessories



533150

PSEN cable M8-8sf, 2m



533151

PSEN cable M8-8sf, 5m



533152

PSEN cable M8-8sf, 10m



533153

PSEN cable M8-8sf, 20m



533154

PSEN cable M8-8sf, 30m



533155

PSEN cable M8-8sf M8-sm, 0.5m



533156

PSEN cable M8-8sf M8-8sm, 1m



533157

PSEN cable M8-8sf M8-8sm, 2m



535120

PSEN ix1 Interface for 4 PSEN 1



540329

PSEN converter M8-8sf -- M12-8sm

---