

PSEN cable M8-8sf M8-sm, 0.5m

533155



PSEN cable M8/8-pin connector female on M8/8-pin connector, length: 0.5 m.

Technical details

Rated current:	1.5 A
Number of conductors:	8
Shielding:	No
Conductor cross section:	0,14
Drag capacity:	Yes
Length cable:	0.50 m
Certifications:	cULus Recognized
Ambient temperature:	-25 - 80 °C
Degree of protection connector 1:	IP67
Degree of protection connector 2:	IP67