

## PSEN cable M12-5sf VA 5m

533170



Connecting cable with plug, M12-5 pin connector, stainless steel, degree of protection IP69K, material cable PVC, UL 105°C, cable length 5m

## Technical details

Rated current:	4.0 A
Number of conductors:	5
Shielding:	No
Conductor cross section:	0,34
Drag capacity:	Yes
Length cable:	5.00 m
Certifications:	cULus Listed;ECOLAB
Ambient temperature:	-40 - 105 °C
Degree of protection connector 1:	IP69K