



Fieldbus modul Modbus/TCP for Safety Device Diagnostics

Technical details

Certifications:	CE;cULus Listed
Number of semiconductor outputs:	6
Supply voltage (V):	24,0
Supply voltage type:	DC
Power consumption DC:	2.0 W
Terminal type:	spring-loaded terminal, plug in;Schraubklemme steckbar
Fieldbus interface:	Modbus/TCP
Fieldbus connection:	RJ45
Protection type, housing:	IP20
Width dimension:	45.0 mm
Height dimension:	115.0 mm
Depth dimension:	95.0 mm
Gross weight:	175 g
Net weight:	160 g
Ambient temperature:	0 - 55 °C

Accessories



540120

SDD ES SET SCREW TERMINALS



540121

SDD ES SET SPRING LOADED TERMINALS
