

PSEN cable M12-8sf, 20m

540333



Unshielded cable, PUR with an straight M12 connector (female), 8 pins

## Technical details

Rated current:	2.0 A
Number of conductors:	8
Shielding:	No
Conductor cross section:	0,25
Drag capacity:	Yes
Length cable:	20.00 m
Certifications:	cULus Listed
Ambient temperature:	-25 - 80 °C
Degree of protection connector 1:	IP68