

PSEN cable M12-8sf M12-8sm, 20m

540343



Connection cable for PSENcode, connector female M12, 8-pin, straight outlet and connector M12, 8-pin, straight outlet.

Technical details

| | |
|-----------------------------------|--------------|
| Rated current: | 2.0 A |
| Number of conductors: | 8 |
| Shielding: | No |
| Conductor cross section: | 0,25 |
| Drag capacity: | Yes |
| Length cable: | 20.00 m |
| Certifications: | cULus Listed |
| Ambient temperature: | -25 - 80 °C |
| Degree of protection connector 1: | IP67 |
| Degree of protection connector 2: | IP67 |