

PSEN cable M12-8sf M12-8sm, 1,5m

540347



PSS67 cable, M12 female connector straight to M12 connector straight.

Technical details

Rated current:	2.0 A
Number of conductors:	8
Shielding:	No
Conductor cross section:	0,25
Drag capacity:	Yes
Length cable:	1.50 m
Certifications:	cULus Listed
Ambient temperature:	-25 - 80 °C
Degree of protection connector 1:	IP67
Degree of protection connector 2:	IP67