

PSEN cs3.19n 1 switch

541353




RFID safety switch 2 safe semiconductor outputs, 5-pin M12 connector, one direction of actuation IP67, operating distance 11 mm, Sao = 8 mm, Sar = 20 mm. PU = 1 piece coded switch without actuator.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV;FCC;IC
Sensor principle:	Transponder
Type of coding:	Coded
Number of OSSD outputs:	2
Connection type:	M12, 5pol. male
Supply voltage (V):	24,0
Supply voltage type:	DC
Power consumption DC:	1.0 W
Assured switching distance:	8.0 mm
Assured release distance:	20.0 mm
Protection type, housing:	IP6K9K
Width dimension:	26.0 mm
Height dimension:	37.0 mm
Depth dimension:	18.0 mm
Gross weight:	60 g
Net weight:	40 g
Ambient temperature:	-25 - 55 °C

Accessories



541383

PSEN cs3.19-OSSD2 1actuator

Optional accessories



380208

PSS67 Cable M12sf M12sm, 3m



380209

PSS67 Cable M12sf M12sm, 5m



380210

PSS67 Cable M12sf M12sm, 10m



380211

PSS67 Cable M12sf M12sm, 30m



380212

PSS67 Cable M12af M12am, 3m



380213

PSS67 Cable M12af M12am, 5m



380214

PSS67 Cable M12af M12am, 10m



380215

PSS67 Cable M12af M12am, 30m



630297

PSEN op cable axial M12 5-pole 30m



630310

PSEN op cable axial M12 5-pole 3m



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630347

PSEN op cable angle M12 5-pole 3m



630348

PSEN op cable angle M12 5-pole 5m



630349

PSEN op cable angle M12 5-pole 10m



630350

PSEN op cable angle M12 5-pole 30m



773600

PDP67 F 8DI ION



380220

PSS67 cable M12-5sf, M12-5sm, 20m



630298

PSEN cable M12-5sf 20m



540130

SDD ES ETH



540132

SDD ES PROFIBUS