

PSEN cs5.13 M12/8 EX 1switch

542055



RFID safety switch 2 safe semiconductor outputs, 5-pin M12 connector, IP67, 4 directions of actuation, Operating distance (direction of actuation square): 11 mm, Sao = 8 mm, Sar = 20 mm, PU = 1 piece coded switch, ATEX approval.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);ATEX;TÜV;FCC;IC;ECOLAB;electrosuisse
Sensor principle:	Transponder
Type of coding:	Coded
Number of OSSD outputs:	2
Number of inputs:	2
Connection type:	M12, 8pol. male
Supply voltage (V):	24,0
Supply voltage type:	DC
Power consumption DC:	1.0 W
Protection type, housing:	IP67
Coding level EN ISO 14119 aligned:	gering
Product Material:	PA+GF;Polycarbonat
Pollution degree:	3
Tolerance of supply voltage:	-20 %/+20 %
Overvoltage category:	III
Width dimension:	101.6 mm
Height dimension:	26.4 mm
Depth dimension:	19.0 mm
Gross weight:	78 g
Net weight:	68 g

Ambient temperature:

-25 - 55 °C

Accessories



542085

PSEN cs5.13 M12 EX 1 actuator

Optional accessories



532110

PSEN Winkel / bracket



540319

PSEN cable axial M12 8-pole 3m



540320

PSEN cable axial M12 8-pole 5m



540321

PSEN cable axial M12 8-pole 10m



540322

PSEN cable angle M12 8-pole 3m



540323

PSEN cable angle M12 8-pole 5m



540324

PSEN cable angle M12 8-pole 10m



540325

PSEN cable angle M12 8-pole 30m



540326

PSEN cable axial M12 8-pole 30m



540331

PSEN T junction (auxiliary contact) M12



773603

PDP67 F 4 code



540340

PSEN cable M12-8sf M12-8sm, 2m



540341

PSEN cable M12-8sf M12-8sm, 5m



540343

PSEN cable M12-8sf M12-8sm, 20m



540344

PSEN cable M12-8sf M12-8sm, 30m



540342

PSEN cable M12-8sf M12-8sm, 10m



540333

PSEN cable M12-8sf, 20m



773613

PDP67 F 4 code VA



540313

PSEN screw M4x20 10pcs



540314

PSEN screw M4x26 10pcs



540130

SDD ES ETH



540132

SDD ES PROFIBUS



532109

PSEN cs bracket stop sliding door



532111

PSEN mag/cs bracket straight



535111

PSEN ix2 F4 code



540315

PSEN Y junction M12 SENSOR



540338

PSEN Y junction M12-M12/M12 PIGTAIL




540316

PSEN Y junction M12 cable channel



540337

PSEN Y junction M8-M12/M12 PIGTAIL



535112

PSEN ix2 F8 code



532108

PSEN cs bracket stop swinging door