

PSEN cs6.2n 1switch

542253



RFID safety switch 2 safe semiconductor outputs, 5-pin M12 connector, IP67, 4 directions of actuation, Operating distance (direction of actuation square): 11 mm, Sao = 8 mm, Sar = 20 mm, PU = 1 piece unique, fully coded switch.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV;FCC;IC;ECOLAB
Sensor principle:	Transponder
Type of coding:	unique coding
Number of OSSD outputs:	2
Connection type:	M12, 5pol. male
Supply voltage (V):	24,0
Supply voltage type:	DC
Power consumption DC:	1.0 W
Protection type, housing:	IP66;IP67
Coding level EN ISO 14119 aligned:	hoch
Product Material:	PA+GF;PBT;Polycarbonat
Pollution degree:	3
Tolerance of supply voltage:	-20 %/+20 %
Overvoltage category:	III
Width dimension:	101.6 mm
Height dimension:	26.4 mm
Depth dimension:	19.0 mm
Gross weight:	78 g
Net weight:	68 g
Ambient temperature:	-25 - 70 °C

Accessories



542183

PSEN cs6.1 M12 1 actuator



542187

PSEN cs6.1 low profile glue 1 actuator



542188

PSEN cs6.1 low profile screw 1 actuator

Optional accessories



380208

PSS67 Cable M12sf M12sm, 3m



380209

PSS67 Cable M12sf M12sm, 5m



380210

PSS67 Cable M12sf M12sm, 10m












380211

PSS67 Cable M12sf M12sm, 30m



380212

PSS67 Cable M12af M12am, 3m

	380213	PSS67 Cable M12af M12am, 5m
	380214	PSS67 Cable M12af M12am, 10m
	380215	PSS67 Cable M12af M12am, 30m
	532110	PSEN Winkel / bracket
	630297	PSEN op cable axial M12 5-pole 30m
	630310	PSEN op cable axial M12 5-pole 3m
	630311	PSEN op cable axial M12 5-pole 5m
	630312	PSEN op cable axial M12 5-pole 10m
	630347	PSEN op cable angle M12 5-pole 3m



630348

PSEN op cable angle M12 5-pole 5m



630349

PSEN op cable angle M12 5-pole 10m



630350

PSEN op cable angle M12 5-pole 30m



773600

PDP67 F 8DI ION



773601

PDP67 F 8DI ION HP



380220

PSS67 cable M12-5sf, M12-5sm, 20m



630298

PSEN cable M12-5sf 20m



773614

PDP67 F 8DI ION VA



773615

PDP67 F 8DI ION HP VA



540313

PSEN screw M4x20 10pcs



540314

PSEN screw M4x26 10pcs



532109

PSEN cs bracket stop sliding door



532111

PSEN mag/cs bracket straight



532108

PSEN cs bracket stop swinging door
