

PSEN cable M12-12sf 30m

570355



Connecting cable with plug, M12-12pin connector, female, 30m PUR-cable, 12x0,25mm²

Technical details

Rated current:	2.0 A
Number of conductors:	12
Shielding:	No
Conductor cross section:	0,25
Drag capacity:	No
Length cable:	30.00 m
Ambient temperature:	-30 - 80 °C
Degree of protection connector 1:	IP67