

## PSEN cable M12-12sf/M12-12sm 10m

570361



Connection cable, M12-12pin Connector (female/male), 10m PUR-cable, 12X0,25mm<sup>2</sup>

### Technical details

Rated current:	2.0 A
Number of conductors:	12
Shielding:	No
Conductor cross section:	0,25
Drag capacity:	No
Length cable:	10.00 m
Ambient temperature:	-30 - 80 °C
Degree of protection connector 1:	IP67
Degree of protection connector 2:	IP67