

PSEN ml s 2.2 switch

570411



Safety gate system with mechanical guard locking; version for serial connection; with power reset; IP67; 12pin M12 pigtail 230mm; 4 LEDs on 3 sides; Applications up to SIL3/PL e/Cat4; Content = 1 unique fully coded Sensor without actuator;

Technical details

Certifications:	CE;cULus Listed;TÜV;FCC;IC
Sensor principle:	Transponder
Type of coding:	unique coding
Number of OSSD outputs:	2
Connection type:	M12, 12pol. male
Suitable for series connection:	Yes
Supply voltage (V):	24,0
Power consumption DC:	1.0 W
Supply voltage type:	DC
Protection type, housing:	IP67
Coding level EN ISO 14119 aligned:	hoch
Width dimension:	40.0 mm
Height dimension:	217.2 mm
Depth dimension:	40.0 mm
Gross weight:	1300 g
Net weight:	950 g
Ambient temperature:	0 - 60 °C

Optional accessories



540319

PSEN cable axial M12 8-pole 3m



540320

PSEN cable axial M12 8-pole 5m



540321

PSEN cable axial M12 8-pole 10m



540326

PSEN cable axial M12 8-pole 30m



540340

PSEN cable M12-8sf M12-8sm, 2m



540341

PSEN cable M12-8sf M12-8sm, 5m



540343

PSEN cable M12-8sf M12-8sm, 20m



540344

PSEN cable M12-8sf M12-8sm, 30m



540342

PSEN cable M12-8sf M12-8sm, 10m

	540333	PSEN cable M12-8sf, 20m
	540347	PSEN cable M12-8sf M12-8sm, 1,5m
	540345	PSEN cable M12-8sf M12-8sm, 0,5m
	540346	PSEN cable M12-8sf M12-8sm, 1m
	570490	PSEN ml mounting plate
	570492	PSEN ml bracket sliding door
	570495	PSEN ml door handle sliding door
	570496	PSEN ml door handle swinging door 70
	570497	PSEN ml door handle swinging door 80



570493

PSEN ml bracket swinging door 70



570494

PSEN ml bracket swinging door 80



570489

PSEN ml / PSENcs Y junction M12



570487

PSEN ml end adapter



570486

PSEN ml Y junction M12



570499

PSEN screw set bracket sliding door



570498

PSEN screw set bracket swinging door



570361

PSEN cable M12-12sf/M12-12sm 10m



570360

PSEN cable M12-12sf/M12-12sm 5m



570355

PSEN cable M12-12sf 30m



570351

PSEN cable M12-12sf 3m



570352

PSEN cable M12-12sf 5m



570359

PSEN cable M12-12sf/M12-12sm 3m



570350

PSEN cable M12-12sf 2m



570354

PSEN cable M12-12sf 20m



570353

PSEN cable M12-12sf 10m



570356

PSEN cable M12-12sf 50m



570357

PSEN cable M12-12sf/M12-12sm 1m



570358

PSEN cable M12-12sf/M12-12sm 2m



570362

PSEN cable M12-12sf/M12-12sm 20m



570462

PSEN ml escape release extension



570471

PSEN ml escape release cordset 2,0m



570474

PSEN ml escape release cordset 3,5m



570472

PSEN ml escape release cordset 2,5m



570470

PSEN ml escape release cordset 1,5m



570473

PSEN ml escape release cordset 3,0m



570460

PSEN ml escape release



570475

PSEN ml escape release cordset 4,0m



570468

PSEN ml escape release cordset 1,0m



570467

PSEN ml escape release cordset 0,75m



570469

PSEN ml escape release cordset 1,25m



570466

PSEN ml escape release cordset 0,5m

570485

PSEN ml actuator center ring

570484

PSEN ml actuator 10° adapter
