

Magnetic safety gate system For applications up to SIL 3/PL e/cat. 4 magnetic holding force 500 N (process protection). Coding: coded; 5-pin M12 male connector; 4 LEDs.



## Technical details

Assured release distance:	15.0 mm
Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV;FCC;IC
Sensor principle:	Transponder
Type of coding:	Coded
Holding force:	500 N
Number of OSSD outputs:	2
Number of inputs:	1
Connection type:	M12, 5pol. male
Supply voltage (V):	24,0
Supply voltage type:	DC
Power consumption DC:	4.8 W
Protection type, housing:	IP67
Housing material:	Anticorodal, hard anodised
Width dimension:	45.0 mm
Height dimension:	122.0 mm
Depth dimension:	44.0 mm
Gross weight:	980 g
Net weight:	940 g
Ambient temperature:	-25 - 55 °C

## Optional accessories



380208

PSS67 Cable M12sf M12sm, 3m



380209

PSS67 Cable M12sf M12sm, 5m



380210

PSS67 Cable M12sf M12sm, 10m



380211

PSS67 Cable M12sf M12sm, 30m



380212

PSS67 Cable M12af M12am, 3m



380213

PSS67 Cable M12af M12am, 5m



380214

PSS67 Cable M12af M12am, 10m



380215

PSS67 Cable M12af M12am, 30m



570550

PSEN sl bracket swing door



570551

PSEN sl bracket sliding door



630297

PSEN op cable axial M12 5-pole 30m



630310

PSEN op cable axial M12 5-pole 3m



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630347

PSEN op cable angle M12 5-pole 3m



630348

PSEN op cable angle M12 5-pole 5m



630349

PSEN op cable angle M12 5-pole 10m



630350

PSEN op cable angle M12 5-pole 30m



773600

PDP67 F 8DI ION

---



540312

PSEN screw M5x20 10pcs

---



380220

PSS67 cable M12-5sf, M12-5sm, 20m

---



630298

PSEN cable M12-5sf 20m

---