

PSEN sg2c-3LPS switch

570805



Safety gate system, safe interlock and safe guard locking device For applications up to SIL CL 3 and PL e. 3 pushbuttons: 1. Illuminated pushbutton for activating the safety gate. 2. Pushbutton for accessing & interlocking the safety gate 3. Section stop pushbutton Delivery scope: Sensing device with pushbuttons (spare part).

Technical details

Certifications:	CE;cULus Listed;TÜV;FCC
Sensor principle:	Transponder
Type of coding:	Coded
Holding force:	2000 N
Number of OSSD outputs:	2
Number of inputs:	2
Connection type:	Federzugklemme steckbar
Supply voltage (V):	24,0
Supply voltage type:	DC
Power consumption DC:	2.0 W
Number of pushbutton:	2
Protection type, housing:	IP54
Number of control elements:	2
Number of section stops:	1
Width dimension:	46.5 mm
Height dimension:	465.0 mm
Depth dimension:	74.5 mm
Gross weight:	1170 g
Net weight:	1080 g
Ambient temperature:	-20 - 55 °C

Accessories



570870

PSEN sg escape release pin



570871

PSEN sg auxiliary release pin



570875

PSEN sg color covers (pushbutton)



570890

PSEN sg2 actuator

Optional accessories



570773

PSEN sg2 cover 2pieces



570777

PSEN sg2c Set spring loaded terminals



570890

PSEN sg2 actuator



570870

PSEN sg escape release pin



570871

PSEN sg auxiliary release pin

570875

PSEN sg color covers (pushbutton)

