

## PSEN sg2c-5LBLE switch

570815



"Safety gate system includes safe interlocking device with guard locking. According to DIN EN60947-5-3. For applications up to SIL CL3 or Ple. Device type: 1. illuminated push button 2. key button 3. illuminated push button 4. illuminated push button 5. E-Stop Scope of delivery: Sensor unit with push buttons (spare)."

### Technical details

Certifications:	CE;cULus Listed;TÜV;FCC
Sensor principle:	Transponder
Type of coding:	Coded
Holding force:	2000 N
Number of OSSD outputs:	2
Number of inputs:	2
Connection type:	Federzugklemme steckbar
Supply voltage (V):	24,0
Supply voltage type:	DC
Power consumption DC:	2.0 W
Number of pushbutton:	2
Protection type, housing:	IP54
Number of emergency stops:	1
Number of control elements:	4
Width dimension:	46.5 mm
Height dimension:	555.0 mm
Depth dimension:	74.5 mm
Gross weight:	1270 g
Net weight:	1180 g
Ambient temperature:	-20 - 55 °C

## Accessories



570870

PSEN sg escape release pin



570871

PSEN sg auxiliary release pin



570875

PSEN sg color covers (pushbutton)



570890


PSEN sg2 actuator

## Optional accessories



570773

PSEN sg2 cover 2pieces



570777

PSEN sg2c Set spring loaded terminals



570890

PSEN sg2 actuator



570870

PSEN sg escape release pin



570871

PSEN sg auxiliary release pin

---

570875

PSEN sg color covers (pushbutton)

