

PSEN op cable axial M12 4-p. shield. 20m

630270



Shielded cable PUR with straight M12 plug. Length 20m

## Technical details

Rated current:	4.0 A
Number of conductors:	4
Shielding:	Yes
Conductor cross section:	0,34
Drag capacity:	No
Length cable:	20.00 m
Ambient temperature:	-25 - 80 °C
Degree of protection connector 1:	IP67