

PSEN cable M12-5sf 20m

630298



Unshielded cable, PUR with an straight M12 connector (female), 5 pins

Technical details

Rated current:	4.0 A
Number of conductors:	5
Shielding:	No
Conductor cross section:	0,25
Drag capacity:	No
Length cable:	20.00 m
Certifications:	cULus Listed
Ambient temperature:	-25 - 80 °C
Degree of protection connector 1:	IP68