

PSEN op2H-s-30-045/1

630722



Safety light curtain, type 2, PL c, hand protection (resolution 30 mm)
Protected field height 450 mm, supply voltage 24 V, connector M12,
sender: 4-pin, receiver: 5-pin, Connection cable not supplied with the unit.

Technical details

| | |
|-----------------------------------|------------------------------------|
| Certifications: | CE;cULus Listed;EAC (Eurasian);TÜV |
| Sensor principle: | Optical |
| Type in accordance with EC 61496: | 2 |
| Number of beams: | 24 |
| Height of protected field: | 450 mm |
| Resolution of safety device: | 30 mm |
| Operating range (m): | 0,2 - 19,0 |
| Reaction time: | 11.00 ms |
| Number of OSSD outputs: | 2 |
| Muting: | No |
| Blanking: | No |
| Supply voltage (V): | 24,0 |
| Supply voltage type: | DC |
| Application in accordance with: | CLC/TS 61496-2;EN 61496-1 |
| Protection type, housing: | IP65 |
| Resolution, protection type: | Hand |
| Width dimension: | 32.3 mm |
| Height dimension: | 533.2 mm |
| Depth dimension: | 36.9 mm |
| Gross weight: | 2500 g |

| | |
|----------------------|-----------|
| Net weight: | 2000 g |
| Ambient temperature: | 0 - 55 °C |

Accessories



630297

PSEN op cable axial M12 5-pole 30m



630303

PSEN op cable axial M12 4-p. shield. 3m



630304

PSEN op cable axial M12 4-p. shield. 5m



630305

PSEN op cable axial M12 4-p. shield. 10m



630306

PSEN op cable angle M12 4-p. shield. 3m



630307

PSEN op cable angle M12 4-p. shield. 5m












630308

PSEN op cable angle M12 4-p. shield. 10m



630309

PSEN op cable axial M12 4-p. shield. 30m

| | | |
|---|--------|--|
|  | 630310 | PSEN op cable axial M12 5-pole 3m |
|  | 630311 | PSEN op cable axial M12 5-pole 5m |
|  | 630312 | PSEN op cable axial M12 5-pole 10m |
|  | 630319 | PSEN op cable angle M12 4-p. shield. 30m |
|  | 630347 | PSEN op cable angle M12 5-pole 3m |
|  | 630348 | PSEN op cable angle M12 5-pole 5m |
|  | 630349 | PSEN op cable angle M12 5-pole 10m |
|  | 630350 | PSEN op cable angle M12 5-pole 30m |
|  | 630298 | PSEN cable M12-5sf 20m |



630365

PSEN op cable angle M12 5-pole 50m



630364

PSEN op cable axial M12 5-pole 50m

Optional accessories



630296

PSEN op cable axial M12 4-pole 30m



630300

PSEN op cable axial M12 4-pole 3m



630301

PSEN op cable axial M12 4-pole 5m



630302

PSEN op cable axial M12 4-pole 10m



630326

PSEN op Bracket kit adjustable



630327

PSEN op Bracket kit antivibration



630340

Laser pointer for PSEN 4/2



630341

PSEN op cable angle M12 4-pole 3m



630342

PSEN op cable angle M12 4-pole 5m



630343

PSEN op cable angle M12 4-pole 10m



630344

PSEN op cable angle M12 4-pole 30m



630346

PSEN op Testpiece H 30mm



630932

PSEN op67-69K-045/1



630901

PSEN op Mirror-060/1



630950

PSEN op Protective Column-060/1



630951

PSEN op Protective Column-090/1



630955

PSEN op Protective Base/1



630956

PSEN op Protective Bracket-4/1



630912

PSEN op Lens Shield-045/1



630960

PSEN op Protective Bracket Mirror/1



630906

PSEN op Mirror Bracket Kit/1



630362

PSEN op cable axial M12 4-pole 50m



630363

PSEN op cable angle M12 4-pole 50m



630366

PSEN op cable axial M12 4-p. shield. 50m



630367

PSEN op cable angle M12 4-p. shield. 50m
