

PSEN op2H-s-30-060/1

630723



Safety light curtain, type 2, PL c, hand protection (resolution 30 mm)
Protected field height 600 mm, supply voltage 24 V, connector M12,
sender: 4-pin, receiver: 5-pin, Connection cable not supplied with the unit.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Sensor principle:	Optical
Type in accordance with EC 61496:	2
Number of beams:	32
Height of protected field:	600 mm
Resolution of safety device:	30 mm
Operating range (m):	0,2 - 19,0
Reaction time:	12.00 ms
Number of OSSD outputs:	2
Muting:	No
Blanking:	No
Supply voltage (V):	24,0
Supply voltage type:	DC
Application in accordance with:	CLC/TS 61496-2;EN 61496-1
Protection type, housing:	IP65
Resolution, protection type:	Hand
Width dimension:	32.3 mm
Height dimension:	683.2 mm
Depth dimension:	36.9 mm
Gross weight:	3360 g

Net weight:	2360 g
Ambient temperature:	0 - 55 °C

Accessories



630297

PSEN op cable axial M12 5-pole 30m



630303

PSEN op cable axial M12 4-p. shield. 3m



630304

PSEN op cable axial M12 4-p. shield. 5m



630305

PSEN op cable axial M12 4-p. shield. 10m



630306

PSEN op cable angle M12 4-p. shield. 3m



630307

PSEN op cable angle M12 4-p. shield. 5m












630308

PSEN op cable angle M12 4-p. shield. 10m



630309

PSEN op cable axial M12 4-p. shield. 30m

	630310	PSEN op cable axial M12 5-pole 3m
	630311	PSEN op cable axial M12 5-pole 5m
	630312	PSEN op cable axial M12 5-pole 10m
	630319	PSEN op cable angle M12 4-p. shield. 30m
	630347	PSEN op cable angle M12 5-pole 3m
	630348	PSEN op cable angle M12 5-pole 5m
	630349	PSEN op cable angle M12 5-pole 10m
	630350	PSEN op cable angle M12 5-pole 30m
	630298	PSEN cable M12-5sf 20m



630365

PSEN op cable angle M12 5-pole 50m



630364

PSEN op cable axial M12 5-pole 50m

Optional accessories



630296

PSEN op cable axial M12 4-pole 30m



630300

PSEN op cable axial M12 4-pole 3m



630301

PSEN op cable axial M12 4-pole 5m



630302

PSEN op cable axial M12 4-pole 10m



630326

PSEN op Bracket kit adjustable



630327

PSEN op Bracket kit antivibration



630340

Laser pointer for PSEN 4/2



630341

PSEN op cable angle M12 4-pole 3m



630342

PSEN op cable angle M12 4-pole 5m



630343

PSEN op cable angle M12 4-pole 10m



630344

PSEN op cable angle M12 4-pole 30m



630346

PSEN op Testpiece H 30mm



630913

PSEN op Lens Shield-060/1



630933

PSEN op67-69K-060/1



630902

PSEN op Mirror-090/1



630950

PSEN op Protective Column-060/1



630951

PSEN op Protective Column-090/1



630955

PSEN op Protective Base/1



630956

PSEN op Protective Bracket-4/1



630960

PSEN op Protective Bracket Mirror/1



630906

PSEN op Mirror Bracket Kit/1



630362

PSEN op cable axial M12 4-pole 50m



630363

PSEN op cable angle M12 4-pole 50m



630366

PSEN op cable axial M12 4-p. shield. 50m



630367

PSEN op cable angle M12 4-p. shield. 50m
