

PSEN op4H-s-30-135/1

630768



Safety light curtain, type 4, PL e, hand protection (resolution 30mm)
Protected field height 1350 mm, supply voltage 24 V, connector M12,
sender: 4-pin, receiver: 8-pin, Connection cable not supplied with the unit.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Sensor principle:	Optical
Type in accordance with EC 61496:	4
Resolution of safety device:	30 mm
Number of beams:	72
Resolution, protection type:	Hand
Height of protected field:	1350 mm
Operating range (m):	0,2 - 19,0
Reaction time:	23.00 ms
Number of OSSD outputs:	2
Blanking:	No
Muting:	No
Supply voltage (V):	24,0
Supply voltage type:	DC
Protection type, housing:	IP65
Application in accordance with:	CLC/TS 61496-2;EN 61496-1
Width dimension:	32.3 mm
Height dimension:	1433.2 mm
Depth dimension:	36.9 mm
Gross weight:	6640 g

Net weight:	4640 g
Ambient temperature:	0 - 55 °C

Optional accessories



540319

PSEN cable axial M12 8-pole 3m



540320

PSEN cable axial M12 8-pole 5m



540321

PSEN cable axial M12 8-pole 10m



540322

PSEN cable angle M12 8-pole 3m



540323

PSEN cable angle M12 8-pole 5m



540324

PSEN cable angle M12 8-pole 10m





540325

PSEN cable angle M12 8-pole 30m



540326

PSEN cable axial M12 8-pole 30m

	630296	PSEN op cable axial M12 4-pole 30m
	630300	PSEN op cable axial M12 4-pole 3m
	630301	PSEN op cable axial M12 4-pole 5m
	630302	PSEN op cable axial M12 4-pole 10m
	630303	PSEN op cable axial M12 4-p. shield. 3m
	630304	PSEN op cable axial M12 4-p. shield. 5m
	630305	PSEN op cable axial M12 4-p. shield. 10m
	630306	PSEN op cable angle M12 4-p. shield. 3m
	630307	PSEN op cable angle M12 4-p. shield. 5m



630308

PSEN op cable angle M12 4-p. shield. 10m



630309

PSEN op cable axial M12 4-p. shield. 30m



630313

PSEN op cable axial M12 8-p. shield. 3m



630314

PSEN op cable axial M12 8-p. shield. 5m



630315

PSEN op cable axial M12 8-p. shield. 10m



630316

PSEN op cable angle M12 8-p. shield. 3m



630317

PSEN op cable angle M12 8-p. shield. 5m



630318

PSEN op cable angle M12 8-p. shield. 10m



630319

PSEN op cable angle M12 4-p. shield. 30m



630326

PSEN op Bracket kit adjustable



630327

PSEN op Bracket kit antivibration



630328

PSEN op cable axial M12 8-p. shield. 30m



630329

PSEN op cable angle M12 8-p. shield. 30m



630340

Laser pointer for PSEN 4/2



630341

PSEN op cable angle M12 4-pole 3m



630342

PSEN op cable angle M12 4-pole 5m







630343

PSEN op cable angle M12 4-pole 10m



630344

PSEN op cable angle M12 4-pole 30m

	630346	PSEN op Testpiece H 30mm
	630904	PSEN op Mirror-165/1
	630918	PSEN op Lens Shield-135/1
	630955	PSEN op Protective Base/1
	630953	PSEN op Protective Column-165/1
	630954	PSEN op Protective Column-190/1
	630956	PSEN op Protective Bracket-4/1
	630938	PSEN op67-69K-135/1
	630960	PSEN op Protective Bracket Mirror/1



630906

PSEN op Mirror Bracket Kit/1



630362

PSEN op cable axial M12 4-pole 50m



630363

PSEN op cable angle M12 4-pole 50m



630369

PSEN op cable angle M12 8-p. shield. 50m



630366

PSEN op cable axial M12 4-p. shield. 50m



630367

PSEN op cable angle M12 4-p. shield. 50m



630368

PSEN op cable axial M12 8-p. shield. 50m