

PSEN op2B-3-080/1

630805










Safety light curtain, type 2, PL c, body protection Protected field height 800 mm, supply voltage 24 V, connector M12, sender: 4-pin, receiver: 5-pin, with Muting function, Connection cable not supplied with the unit.

Technical details

Certifications:	CE;cULus Listed;TÜV
Sensor principle:	Optical
Type in accordance with EC 61496:	2
Number of beams:	3
Resolution of safety device:	415 mm
Height of protected field:	815 mm
Operating range (m):	0,5 - 50,0
Reaction time:	14.00 ms
Number of OSSD outputs:	2
Blanking:	No
Muting:	Yes
Cascading:	No
Supply voltage (V):	24,0
Supply voltage type:	DC
Application in accordance with:	EN 61496-1;IEC 61496-2
Resolution, protection type:	Body
Protection type, housing:	IP65
Width dimension:	35.0 mm
Height dimension:	953.0 mm
Depth dimension:	41.2 mm

Gross weight:	4100 g
Net weight:	3500 g
Ambient temperature:	-10 - 55 °C

Optional accessories

	630282	PSEN op cable M12 4-p. 0,75m L-Muting
	630295	PSEN op cablesset
	630296	PSEN op cable axial M12 4-pole 30m
	630297	PSEN op cable axial M12 5-pole 30m
	630300	PSEN op cable axial M12 4-pole 3m
	630301	PSEN op cable axial M12 4-pole 5m
	630302	PSEN op cable axial M12 4-pole 10m



630310

PSEN op cable axial M12 5-pole 3m



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630313

PSEN op cable axial M12 8-p. shield. 3m



630314

PSEN op cable axial M12 8-p. shield. 5m



630315

PSEN op cable axial M12 8-p. shield. 10m



630326

PSEN op Bracket kit adjustable



630327

PSEN op Bracket kit antivibration



630328

PSEN op cable axial M12 8-p. shield. 30m



630340

Laser pointer for PSEN 4/2



630950

PSEN op Protective Column-060/1



630951

PSEN op Protective Column-090/1



630952

PSEN op Protective Column-120/1



630955

PSEN op Protective Base/1



630953

PSEN op Protective Column-165/1



630954

PSEN op Protective Column-190/1



630298

PSEN cable M12-5sf 20m



630362

PSEN op cable axial M12 4-pole 50m



630364

PSEN op cable axial M12 5-pole 50m



630368

PSEN op cable axial M12 8-p. shield. 50m



630962

PSEN op Protective Column 3-080/1



630961

PSEN op Protective Column 2-050/1



630964

PSEN op Protective Column 4-120/1



630963

PSEN op Protective Column 4-090/1



630822

PSEN op2.3 L-Reflex



630820

PSEN op2.1 L-Muting Set



630821

PSEN op2.2 T-Muting Set



630824

PSEN op muting bracket kit



630823

PSEN op2.4 L-Reflector



630831

PSEN op3.1 Receiver NO/NC M12



630830

PSEN op3.3 Reflex NO/NC M12



630832

PSEN op3.2 Emitter M12