

PSEN op2H-A-30-045/1

631041



Safety light curtain, type 2, PL c, hand protection (resolution 30mm)
Protected field height 450 mm. Features: Muting, no dead zones UB 24 V DC; connector M12, sender: 5-pin, receiver: 12-pin/5-pin. No pigtail cables are supplied with the unit, order no.: Sender: 631055, receiver muting: 631057.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Sensor principle:	Optical
Type in accordance with EC 61496:	2
Number of beams:	24
Height of protected field:	450 mm
Operating range (m):	0,2 - 20,0
Reaction time:	14.00 ms
Number of OSSD outputs:	2
Muting:	Yes
Blanking:	No
Cascading:	No
Supply voltage (V):	24,0
Supply voltage type:	DC
Protection type, housing:	IP65
Application in accordance with:	EN 61496-1;IEC 61496-2
Resolution of safety device:	30 mm
Width dimension:	35.0 mm
Height dimension:	456.3 mm
Depth dimension:	40.8 mm
Gross weight:	2700 g

Net weight:	1050 g
Ambient temperature:	0 - 50 °C

Accessories



630297 PSEN op cable axial M12 5-pole 30m



630310 PSEN op cable axial M12 5-pole 3m



630311 PSEN op cable axial M12 5-pole 5m



630312 PSEN op cable axial M12 5-pole 10m



630298 PSEN cable M12-5sf 20m



630364 PSEN op cable axial M12 5-pole 50m



631056 PSEN op pigtail receiver b



631057 PSEN op pigtail receiver m



631055

PSEN op pigtail emitter



631085

PSEN op cable axial M12 12-pole 50m



631083

PSEN op cable axial M12 12-pole 20m



631082

PSEN op cable axial M12 12-pole 10m



631084

PSEN op cable axial M12 12-pole 30m



631080

PSEN op cable axial M12 12-pole 3m



631081

PSEN op cable axial M12 12-pole 5m