

## PSEN op Ethernet cable 3m

631072



Ethernet cable, M12-4pin D-coded and RJ45 connector, 3m, to connect the PSEN op Advanced Programming Adapter or the PSENscan with a PC.

### Technical details

Rated current:	1.5 A
Number of conductors:	4
Shielding:	No
Conductor cross section:	0,14
Drag capacity:	No
Length cable:	3.00 m
Ambient temperature:	-20 - 55 °C
Degree of protection connector 1:	IP67