

## PSEN op cable axial M12 12-pole 20m

631083



Unshielded cable PUR with straight M12 connector, 12-pin, length: 20 m.

### Technical details

Rated current:	1.5 A
Number of conductors:	12
Shielding:	No
Conductor cross section:	0,14
Drag capacity:	Yes
Length cable:	20.00 m
Certifications:	cULus Listed
Ambient temperature:	-30 - 80 °C
Degree of protection connector 1:	IP67