

PSEN op2H-SL-24-120/1

631107



Safety light curtain, type 2 ,PL c, hand protection (resolution 24 mm)  
 Protected field height 1200 mm, supply voltage 24 V, without dead zone  
 Connector: M12, sender: 5-pole, receiver 5-pole Connection cable not  
 supplied with the unit.

## Technical details

Certifications:	CE;cULus Listed;TÜV
Product version:	1.0
Type in accordance with EC 61496:	2
Height of protected field:	1200 mm
Number of beams:	64
Sensor principle:	Optical
Operating range (m):	0,2 - 6,0
Reaction time:	13.00 ms
Number of OSSD outputs:	2
Muting:	No
Supply voltage (V):	24,0
Supply voltage type:	DC
Protection type, housing:	IP65
Application in accordance with:	EN 61496-1;IEC 61496-2
Resolution of safety device:	24 mm
Width dimension:	15.4 mm
Height dimension:	1200.0 mm
Depth dimension:	32.6 mm
Gross weight:	2350 g
Net weight:	1400 g

Ambient temperature:

0 - 55 °C

## Optional accessories



630310

PSEN op cable axial M12 5-pole 3m



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630904

PSEN op Mirror-165/1



630298

PSEN cable M12-5sf 20m



631183

PSEN op SL cascading 0,1m



631180

PSEN op SL Bracket C



631181

PSEN op SL Bracket L



631182

PSEN op SL Bracket O



631184

PSEN op SL cascading 0,5m



631185

PSEN op SL cascading 1m



631186

PSEN op SL Testpiece F 24 mm

---