

PSEN op4F-SL-14-120/1

631160



Safety light curtain, type 4 ,PL e, finger protection (resolution 14 mm)
 Protected field height 1200 mm, supply voltage 24 V, without dead zone
 Connector: M12, sender: 5-pole, receiver 5-pole Connection cable not
 supplied with the unit.

Technical details

| | |
|-----------------------------------|------------------------|
| Certifications: | CE;cULus Listed;TÜV |
| Product version: | 1.0 |
| Type in accordance with EC 61496: | 4 |
| Height of protected field: | 1200 mm |
| Number of beams: | 120 |
| Sensor principle: | Optical |
| Operating range (m): | 0,2 - 6,0 |
| Reaction time: | 17.00 ms |
| Number of OSSD outputs: | 2 |
| Muting: | No |
| Supply voltage (V): | 24,0 |
| Supply voltage type: | DC |
| Protection type, housing: | IP65 |
| Application in accordance with: | EN 61496-1;IEC 61496-2 |
| Resolution of safety device: | 14 mm |
| Width dimension: | 15.4 mm |
| Height dimension: | 1200.0 mm |
| Depth dimension: | 32.6 mm |
| Gross weight: | 2350 g |
| Net weight: | 1400 g |

Ambient temperature:

0 - 55 °C

Optional accessories



630310

PSEN op cable axial M12 5-pole 3m



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630345

PSEN op Testpiece F 14mm



630904

PSEN op Mirror-165/1



630298

PSEN cable M12-5sf 20m



631183

PSEN op SL cascading 0,1m



631180

PSEN op SL Bracket C



631181

PSEN op SL Bracket L



631182

PSEN op SL Bracket O



631184

PSEN op SL cascading 0,5m



631185

PSEN op SL cascading 1m
