

PSEN opII4H-s-30-015

632060

Safety light curtain, type 4 ,PL e, hand protection (resolution 30 mm)  
Protected field height 150 mm, supply voltage 24 V. Connector: M12,  
sender: 5-pole, receiver 5-pole Connection cable not supplied with the unit.



## Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV;KOSHA
Sensor principle:	Infrared
Type in accordance with EC 61496:	4
Number of beams:	8
Height of protected field:	150 mm
Operating range (m):	0,2 - 18,0
Reaction time:	5.20 ms
Number of OSSD outputs:	2
Muting:	No
Blanking:	No
Cascading:	No
Protection type, housing:	IP65
Supply voltage (V):	24,0
Supply voltage type:	DC
Resolution of safety device:	30 mm
Application in accordance with:	EN 61496-1;EN 61496-2
Width dimension:	35.0 mm
Height dimension:	229.0 mm
Depth dimension:	40.0 mm
Gross weight:	1645 g

Net weight:	765 g
Ambient temperature:	-10 - 60 °C

## Accessories



632019

PSEN opII Testpiece H 30 mm

## Optional accessories



380208

PSS67 Cable M12sf M12sm, 3m



380209

PSS67 Cable M12sf M12sm, 5m



380210

PSS67 Cable M12sf M12sm, 10m



380211

PSS67 Cable M12sf M12sm, 30m



380212

PSS67 Cable M12af M12am, 3m



380213

PSS67 Cable M12af M12am, 5m



380214

PSS67 Cable M12af M12am, 10m



380215

PSS67 Cable M12af M12am, 30m



630297

PSEN op cable axial M12 5-pole 30m



630310

PSEN op cable axial M12 5-pole 3m



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630347

PSEN op cable angle M12 5-pole 3m



630348

PSEN op cable angle M12 5-pole 5m



630349

PSEN op cable angle M12 5-pole 10m



630350

PSEN op cable angle M12 5-pole 30m



380220

PSS67 cable M12-5sf, M12-5sm, 20m



630910

PSEN op Lens Shield-015/1



630950

PSEN op Protective Column-060/1



630951

PSEN op Protective Column-090/1



630952

PSEN op Protective Column-120/1



630955

PSEN op Protective Base/1



630957

PSEN op Protective Bracket-6/1



630953

PSEN op Protective Column-165/1



630954

PSEN op Protective Column-190/1



630956

PSEN op Protective Bracket-4/1



630298

PSEN cable M12-5sf 20m



630365

PSEN op cable angle M12 5-pole 50m



630364

PSEN op cable axial M12 5-pole 50m



632015

PSEN opII Bracket Kit



632007

PSEN opII mirror column-060 Set



632011

PSEN opII mirror column-195 Set




632008

PSEN opII mirror column-090 Set



632010

PSEN opII mirror column-165 Set



632009

PSEN opII mirror column-120 Set



632014

PSEN opII Laserpointer



632017

PSEN opII Adv Bracket Kit-3



632016

PSEN opII Adv Bracket Kit-2



632032

PSEN opII mirror column-060



632033

PSEN opII mirror column-090



632035

PSEN opII mirror column-165



632036

PSEN opII mirror column-195



632034

PSEN opII mirror column-120

---