

PSEN opII4B-s-170-150

632125



Safety light curtain, type 4, PL e, body protection (resolution 170mm) protected field height 1500mm, supply voltage 24 V, operating range 0,2-15m, Connector: M12, emitter: 5-pole, receiver 5-pole, connection cable is not in delivery.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV;KOSHA
Sensor principle:	Infrared
Protection type, housing:	IP65
Type in accordance with EC 61496:	4
Number of beams:	10
Height of protected field:	1500 mm
Operating range (m):	0,2 - 15,0
Reaction time:	5.40 ms
Number of OSSD outputs:	2
Muting:	No
Blanking:	No
Cascading:	No
Supply voltage (V):	24,0
Supply voltage type:	DC
Resolution of safety device:	170 mm
Application in accordance with:	EN 61496-1;EN 61496-2
Width dimension:	35.0 mm
Height dimension:	1504.0 mm
Depth dimension:	40.0 mm
Gross weight:	6745 g

Net weight:

4232 g

Ambient temperature:

-10 - 60 °C

Optional accessories



380208

PSS67 Cable M12sf M12sm, 3m



380209

PSS67 Cable M12sf M12sm, 5m



380210

PSS67 Cable M12sf M12sm, 10m



380211

PSS67 Cable M12sf M12sm, 30m



380212

PSS67 Cable M12af M12am, 3m



380213

PSS67 Cable M12af M12am, 5m












380214

PSS67 Cable M12af M12am, 10m



380215

PSS67 Cable M12af M12am, 30m

	630297	PSEN op cable axial M12 5-pole 30m
	630310	PSEN op cable axial M12 5-pole 3m
	630311	PSEN op cable axial M12 5-pole 5m
	630312	PSEN op cable axial M12 5-pole 10m
	630347	PSEN op cable angle M12 5-pole 3m
	630348	PSEN op cable angle M12 5-pole 5m
	630349	PSEN op cable angle M12 5-pole 10m
	630350	PSEN op cable angle M12 5-pole 30m
	380220	PSS67 cable M12-5sf, M12-5sm, 20m



630919

PSEN op Lens Shield-150/1



630955

PSEN op Protective Base/1



630957

PSEN op Protective Bracket-6/1



630953

PSEN op Protective Column-165/1



630954

PSEN op Protective Column-190/1



630956

PSEN op Protective Bracket-4/1



630298

PSEN cable M12-5sf 20m



630365

PSEN op cable angle M12 5-pole 50m



630364

PSEN op cable axial M12 5-pole 50m



632015

PSEN opII Bracket Kit

632011

PSEN opII mirror column-195 Set



632010

PSEN opII mirror column-165 Set



632014

PSEN opII Laserpointer



632017

PSEN opII Adv Bracket Kit-3



632016

PSEN opII Adv Bracket Kit-2



632035

PSEN opII mirror column-165



632036

PSEN opII mirror column-195