

PSEN sc L 5.5 08-12

6D000013



Light - Model, 40mm / 70mm detection capability, muting, override, EDM, restart applications according to EN ISO 61496-3, vertical applications, reference points, measurement date output (UDP), exchangeable memory block, fast replacement; 5.5m safety zone; 1 safety zone in parallel active, 1 warning zone in parallel active, 3 zone set switches, 10 configurable zone sets

## Technical details

Certifications:	CE;cULus Listed;TÜV
Operating range warning zone:	40 m
Rotation time:	30 ms
Selectable resolutions:	70 mm
No. of safety zones simultaneous mon.:	1
No. of zones simultaneous monitoring:	2
Number of zone configurations:	10
Width dimension:	102.0 mm
Height dimension:	152.0 mm
Depth dimension:	112.5 mm
Gross weight:	2140 g
Net weight:	1530 g
Ambient temperature:	0 - 50 °C

## Accessories



540319

PSEN cable axial M12 8-pole 3m



540320

PSEN cable axial M12 8-pole 5m



540321

PSEN cable axial M12 8-pole 10m

---



540326

PSEN cable axial M12 8-pole 30m

---



6D000004

PSEN sc bracket H

---



6D000002

PSEN sc bracket PR

---



6D000003

PSEN sc bracket P

---



570355

PSEN cable M12-12sf 30m

---



570351

PSEN cable M12-12sf 3m

---



570352

PSEN cable M12-12sf 5m

---



570350

PSEN cable M12-12sf 2m

---



570354

PSEN cable M12-12sf 20m



570353

PSEN cable M12-12sf 10m



570356

PSEN cable M12-12sf 50m



6D000010

PSEN sc bracket F



6D000011

PSEN sc bracket C

## Optional accessories



6D000006

PSEN sc memory 08-12