

PNOZ s60 24-48VACDC 3n/o 1n/c 6so

750600



PNOZsigma voltage monitoring relay for applications up to PLe acc. EN ISO 13849-1 and SIL cl 3 acc. EN IEC 62061, UB = 24-48VACDC, Outputs: 3 n/o, 1 n/c, 6 so, width: 90mm, plug-in terminals of screw type, expandable with PNOZsigma contact expansions

Technical details

Application options:	Safe voltage monitoring
Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV;CCC
Operating modes:	Automatic reset;Dual-channel;Manual reset;Self test
Standards:	EN 60204-1;EN 62061;EN ISO 13849-1;EN ISO 14119;VDE 0113-1
Supply voltage type:	AC/DC
Supply voltage (V):	24,0 - 48,0
Max. current at DC13 I (6 cycles/min):	5.0 A
Max. current at AC15:	3.0 A
Measuring circuit frequency range:	50 - 60
Terminal type:	Screw terminal
Number of inputs:	6
Number of instantaneous safety contacts:	3
Number of delayed safety contacts:	0
Height dimension:	98.0 mm
Width dimension:	90.0 mm
Depth dimension:	120.0 mm
Ambient temperature:	-10 - 55 °C
Gross weight:	679 g
Net weight:	669 g